




# Stainless Clevis Pin With Hole

## Clevis Joints & Clips



**R3456**

CLEVIS JOINTS & CLIPS

### Material

Stainless steel (1.4305, X8CrNiS18-9), for sizes 6-8: stainless steel (1.4567, X3CrNiCu18-9-4).

### Tips

For use with clevis joints R3402 and R3403, for split cotter pins to suit see part number P1241.

For washers see part number P0330.A2.

### Technical Notes

Designed for use with clevis joints.

Order No.	d <sub>1</sub> tol. h11	d <sub>2</sub> tol. h14	d <sub>3</sub> tol. H14	l <sub>1</sub> tol. js15	l <sub>2</sub> +0.5	l <sub>3</sub> tol. js14	l <sub>4</sub>	Weight g
R3456.005	5	8	1.2	15	12.3	1.5	0.5	2.6
R3456.006	6	9	1.6	18	15.3	1.5	0.5	4.6
R3456.008	8	12	2.0	23	19.5	2.0	1.0	10.0
R3456.010	10	14	3.2	29	24.5	2.0	1.0	19.0
R3456.012	12	17	4.0	35	29.5	3.0	1.5	34.0
R3456.014	14	19	4.0	40	32.5	3.0	1.5	53.0
R3456.016	16	21	4.0	45	38.2	3.0	-	73.0
R3456.020	20	28	5.0	53	47.0	4.0	-	139.0
R3456.025	25	34	6.3	67	59.0	5.5	-	266.0



## Parts overview

### Clevis Joints

Stocked to DIN 71752 in steel and stainless steel. Plain clevis joints available in right and left hand threads zinc plated steel and stainless steel. Steel sizes from M4 up to M48. Stainless sizes from M4 up to M27.



### Clevis Mating Pieces

These are designed to fit in between our clevis joints to create a linkage where an angular offset is required. Available in zinc plated steel and stainless steel. Sizes M4 up to M20.



### Clevis Pins and Clips

Various styles of pins and clips to suit clevis joints in zinc plated steel and stainless steel. Sizes available to suit all sizes of clevis joints that we offer.



### Clevis Retention Clips

These are the most popular type of clip used with our clevis joints. They create a neat compact assembly, only available in zinc plated steel. Size available for clevis joints from 4mm up to 20mm.



### Male Clevis Joints

Stocked in zinc plated steel and stainless steel, right and left hand threads. Sizes M6 up to M20.





# Clevis Joints

## set-up options

## Materials Handling

**Clevis with retention clip**  
**65630 and 65684**



**Clevis with clevis pin, washer and cotter pin**  
**65660 and 65674**



### Zinc plated steel

**Clevis with clevis pin** **65664**  
**Safety fastener 65680**



**Clevis with clevis pin and circlips** **65666**  
and **65678**



**Clevis with clevis pin, washer and cotter pin**  
**65661 and 65675**



### Stainless steel

**Clevis with 65652**  
**mating piece**  
and **65684** clevis  
retention clip



**Clevis with 65880**  
**rod end and 65684**  
clevis retention clip



### Assembly options

## Tensile tests, statistically to failure (break)

Clevis joints axially loaded.

### Clevises M6 - M42

Leaded low carbon steel (AISI 12L14, 1.0718).

### Material

Clevis size	F min (kN)	F max (kN)	F average value (kN)	Avg. force when clevis starts to deform (kN)
6 x 24 M 6	16,0	19,5	17,6	15,3
8 x 32 M 8	33,2	35,6	34,6	29,3
10 x 40 M10	42,0	52,0	47,5	41,3
12 x 48 M12	53,0	68,5	61,1	50,2
14 x 56 M14	60,5	64,5	63,0	48,8
16 x 64 M16	133,5	146,0	140,2	115
20 x 40 M20	194,5	234,0	213,5	176
25 x 50 M25	311,0	336,0	328,0	260
30 x 60 M30	428,0	450,0	440,6	343
36 x 72 M36	566,0	573,0	569,5	300
35 x 72 M36	561,2	567,9	564,6	370
42 x 84 M42	904,6	904,6	904,6	420

Important note: values in this table are indicative only and should only be used as a rough guide. The Company cannot foresee the intended applications of their products and we accept no liability for any actions taken by third parties. Customers are advised to use their own safety factors and/or perform their own testing on the clevis joint to ensure it meets requirements for their application.