



### R3528

BALL & SOCKET JOINTS

#### Material

Stainless steel (AISI 304)

#### Technical Notes

To DIN 71803 Form C

\*M14x1.5 is a fine pitch thread.

Order No.	d <sub>1</sub> tol. H9	d <sub>2</sub>	d <sub>3</sub> +0.0 -0.2	h <sub>1</sub> ±0.3	h <sub>2</sub> ±0.3	h <sub>3</sub> ±0.3	h <sub>4</sub> +0.4 -0.0	h <sub>5</sub> max.	A/F	Weight g
R3528.005	8.0	M5	8.0	9.0	10.2	12.5	2.0	4.0	7.0	4.5
R3528.006	10.0	M6	10.0	11.0	12.5	15.5	2.2	4.0	8.0	8.5
R3528.008	13.0	M8	13.0	13.0	16.5	18.5	2.4	5.3	11.0	17.7
R3528.010	16.0	M10	16.0	16.0	20.0	23.0	2.7	7.3	13.0	35.0
R3528.012	16.0	M12	16.0	16.0	20.0	23.0	2.7	7.3	13.0	35.0
R3528.014	19.0	M14 x 1.5*	19.0	20.0	28.0	28.5	3.0	10.8	16.0	71.2
R3528.015	19.0	M14	19.0	20.0	28.0	28.5	3.0	10.8	16.0	71.2
R3528.016	19.0	M16	19.0	20.0	28.0	28.5	3.0	10.8	16.0	71.2