





Welding Studs stainless steel

Turnbuckles



R3868

TURNBUCKLES

Material

Stainless steel (A4).

Technical Notes

To DIN 34828.

Important Notes

**Turnbuckles are not to be used for lifting.
Only suitable for use in tension.**

Order No.	Thread hand	d ₁	l ₁	l ₂	Weight kg
R3868.R006-A4	Right	M 6	120	60	0.02
R3868.R008-A4	Right	M 8	120	65	0.04
R3868.R010-A4	Right	M10	150	75	0.07
R3868.R012-A4	Right	M12	150	75	0.11
R3868.R014-A4	Right	M14	165	80	0.15
R3868.R016-A4	Right	M16	200	100	0.26
R3868.R020-A4	Right	M20	220	120	0.44
R3868.R024-A4	Right	M24	260	150	0.76
R3868.R030-A4	Right	M30	260	160	1.20
R3868.R036-A4	Right	M36	300	180	2.10
R3868.L006-A4	Left	M 6	120	60	0.02
R3868.L008-A4	Left	M 8	120	65	0.04
R3868.L010-A4	Left	M10	150	75	0.07
R3868.L012-A4	Left	M12	150	75	0.11
R3868.L014-A4	Left	M14	165	80	0.15
R3868.L016-A4	Left	M16	200	100	0.26
R3868.L020-A4	Left	M20	220	120	0.44
R3868.L024-A4	Left	M24	260	150	0.76
R3868.L030-A4	Left	M30	260	160	1.20
R3868.L036-A4	Left	M36	300	180	2.10