




# Spur Gears - Module 0.75 - Stainless

stainless steel - 10 teeth



**R5126**

STANDARD SPUR GEARS

**Material**

Stainless steel (SUS 304, JIS G 4303).  
Accuracy to JIS B 1702-1 (ISO) class 9.

**Technical Notes**

20° pressure angle, full depth tooth.  
Amount of backlash when assembling

gears = 0,015 - 0,045mm.

**Tips**

For module 0.75 stainless steel gears with more teeth, see R5128 & R5129.  
Max. allowable torque (Nm) is based on standard operating conditions (see tech-

nical pages) with a safety factor of 1.2. For non standard applications apply a suitable safety factor depending on frequency of use, type of working etc.

Order No.	Module	No. of teeth z	Pitch dia. d <sub>1</sub>	d <sub>2</sub>	w <sub>1</sub>	d <sub>3</sub> tol. H8	l <sub>1</sub>	l <sub>2</sub>	Torque Nm max.	Weight g
R5126.075-010	m 0.75	10	7.5	9	8	9	55	47	0.52	26.5