





Ball Bearing - Wire, Duplex Profile

duplex profile, drawn raceway

Ring Bearings



fitted dimensions



R4240

RING BEARINGS

Material

Hardened corrosion resistant steel wire and ball bearings (in plastic cage).

surface-solid settings or can be set by matching with spacers.

competitive. Please ask us to 'cross reference' if required.

Technical Notes

Play in the bearings can be adjusted via the

Tips

Our wire bearings are compatible with most other manufacturers and are very cost

Larger sizes on next page.

Order No.	d	D _L	h	Dyn. load C kN max.	Dyn. load C ₀ kN max.	Weight kg
R4240.0100	87.05	100	12.95	15.0	32.0	0.20
R4240.0105	92.05	105	12.95	15.4	33.6	0.21
R4240.0110	97.05	110	12.95	15.7	35.2	0.22
R4240.0115	102.05	115	12.95	16.1	36.8	0.23
R4240.0120	107.05	120	12.95	16.4	38.4	0.24
R4240.0125	112.05	125	12.95	16.8	40.0	0.25
R4240.0130	117.05	130	12.95	17.1	41.6	0.26
R4240.0135	122.05	135	12.95	17.4	43.2	0.27
R4240.0140	127.05	140	12.95	17.7	44.8	0.27
R4240.0145	132.05	145	12.95	18.1	46.4	0.28
R4240.0150	137.05	150	12.95	18.4	48.0	0.29
R4240.0155	142.05	155	12.95	18.7	49.6	0.30
R4240.0160	147.05	160	12.95	19.0	51.2	0.31
R4240.0165	152.05	165	12.95	19.3	52.8	0.32
R4240.0170	157.05	170	12.95	19.6	54.4	0.33
R4240.0175	162.05	175	12.95	19.9	56.0	0.34
R4240.0180	167.05	180	12.95	20.1	57.6	0.35
R4240.0185	172.05	185	12.95	20.4	59.2	0.36
R4240.0190	177.05	190	12.95	20.7	60.8	0.37
R4240.0195	182.05	195	12.95	21.0	62.4	0.38
R4240.0200	187.05	200	12.95	21.2	64.0	0.39
R4240.0205	192.05	205	12.95	21.5	65.6	0.40
R4240.0210	197.05	210	12.95	21.7	67.2	0.41
R4240.0215	202.05	215	12.95	22.0	68.8	0.42
R4240.0220	207.05	220	12.95	22.3	70.4	0.43
R4240.0225	212.05	225	12.95	22.5	72.0	0.44
R4240.0230	217.05	230	12.95	22.8	73.6	0.45
R4240.0235	222.05	235	12.95	23.0	75.2	0.46
R4240.0240	227.05	240	12.95	23.2	76.8	0.47
R4240.0245	232.05	245	12.95	23.5	78.4	0.48
R4240.0250	237.05	250	12.95	23.7	80.0	0.49



Order No.	d	D _L	h	Dyn. load C kN max.	Dyn. load C ₀ kN max.	Weight kg
R4240.0255	242.05	255	12.95	24.0	81.6	0.50
R4240.0260	247.05	260	12.95	24.2	83.2	0.51
R4240.0265	252.05	265	12.95	24.4	84.8	0.52
R4240.0270	257.05	270	12.95	24.7	86.4	0.53
R4240.0275	262.05	275	12.95	24.9	88.0	0.54
R4240.0280	267.05	280	12.95	25.1	89.6	0.55
R4240.0285	272.05	285	12.95	25.3	91.2	0.56
R4240.0290	277.05	290	12.95	25.6	92.8	0.57
R4240.0295	282.05	295	12.95	25.8	94.4	0.58