

female

# Anti-Vibration Components



#### Material

Rubber on silver zinc plated steel (rubber hardness - 65 Shore A).

#### Tips

These anti-vibration cones or bumpers are

used to reduce vibration and shock. Their conical shape ensures that when used in a row, the buffers spread loads over a number of cones - reducing the chances of possible overloading.

#### **Important Notes**

The working load should not exceed 65% of the maximum load.

Order No.	d <sub>1</sub>	h <sub>1</sub>	d <sub>2</sub>	Axial load kgf max.
P2025.020-020	20	20	M 6	70
P2025.025-020	25	20	M 8	100
P2025.030-030	30	30	M 6	150
P2025.050-048	50	48	M10	380
P2025.070-060	70	60	M12	550
P2025.090-074	90	74	M16	1100
P2025.095-082	95	82	M16	1100





**General Anti-vibration Cylinders** 

installation methods for cylinders



### Acceptable loads

Cylindrical mounts are never to be used in tension, they should only be used in axial or radial. Radial loads are however considerably less than axial loads. Parts with small diameters (d<sub>1</sub>) and relatively long lengths (h) cannot accept radial loads.



## Installation



